



Conforme à VDI 6022



## TFP

### FOR CRITICAL AIR CLEANLINESS AND VERY CRITICAL HYGIENE REQUIREMENTS, SUITABLE FOR CEILING INSTALLATION

Pharmaceutical clean room terminal filters as final filter stage with Mini Pleat filter panels for the separation of suspended particles. Used in highly sensitive areas in pharmaceuticals, medicine, and biology

- Mini Pleat filter panels with downstream fluid seals meet the highest hygiene requirements
- Easy, time-saving, and secure filter change
- Diffuser face is held in place by magnets and can be hinged down to facilitate cleaning and validation; filter change without tool
- Robust, welded construction
- Compact construction, suitable for low ceiling heights
- Various diffuser face plates to ideally meet individual requirements
- Horizontal or vertical connection
- Removable spigot for installation into closed ceilings in case of horizontal connection
- For air cleanliness classes 5 to 8 according to ISO 14644-1
- Meets the hygiene requirements of VDI 6022

## Application

Application



- Pharmaceutical clean room terminal filter type TFP for ceiling installation as final filter stage and for air distribution in sensitive areas of the pharmaceutical industry
- Fitting of filter elements for the separation of suspended particles such as aerosols, toxic dusts, viruses and bacteria from the supply or extract air

#### Special characteristics

- Compact construction
- Flush ceiling installation
- Removable spigot for installation into closed ceilings
- Diffuser face plate can be hinged down

## Description

---



#### Variants

- TC: Top entry circular spigot
- SC: Side entry circular spigot
- SCR: Side entry circular spigot, removable

#### Construction

- Sheet steel, powder-coated RAL 9010, pure white

#### Attachments

- FD: Ceiling swirl diffuser
- TDF: Ceiling swirl diffuser

#### Useful additions

- Mini Pleat filter panels (MFP)
- Suitable filter elements to be ordered separately

#### Construction features

- Welded filter casing with sealing frame for fitting filter elements, with a seal on the downstream side
- Mounted pressure measurement points to monitor the operating differential pressure and with internal measuring tube

#### Materials and surfaces

- Casing and diffuser face plate made of sheet steel, powder-coated RAL 9010, pure white

## INFORMACIÓN TÉCNICA



## TFP

<b>TFP – SC – FD / 600 x 198 x 350</b>					
1	2	3	4	5	6

### 1 Type

**TFP** Tilluftsnet for renrom med filter

### 4 Nominell størrelse [mm]

**400**

**500**

**600**

**625**

### 2 Konstruksjonsvariant

**TC** Toppanslutning sirkulær stuss

**SC** Sideanslutning sirkulær stuss

**SCR** Sideanslutning sirkulær stuss, avtagbar

### 5 Stussdiameter [mm]

**D**

### 3 Ventilfront

**FD**

**TDF**

### 6 Høyde på sarg [mm]

**250**

**350**